







Dätwyler Cables

Figure 1: Suspension device LZ 1006

Figure 2: Suspension device LZ 1009

Suspension device LZ 1010

## **Product information**

## Suspension device LZ 1006, 1009 and 1010

The cable width, number of cables (combinations) and travelling height determine the selection of the cable suspension.


In addition to cable width and travelling height, the number of cables (cable combinations) to be mounted determine the selection of the correct suspension device(s). To this end, please note the maximum clamping thickness of the individual suspension parts.

Material

Nylon PA6 Aluminium LZ 1006 / LZ 1009 grey LZ 1010 blue anodised

## **Dimensions**

**Application** 



| Part no. | Product type | Colour | Cable clamping range | width of cable | Screw holes | Figure |
|----------|--------------|--------|----------------------|----------------|-------------|--------|
|          |              |        | max. [mm]            | ≤ [mm]         |             |        |
| 179 813  | LZ 1006      | grey   | 3-12mm               | ≤ 55mm         | 3           | 1      |
| 179 814  | LZ 1009      | grey   | 3-15mm               | ≤ 56 – 79mm    | 4           | 2      |
| 163 354  | LZ 1010      | blue   | 3-22mm               | ≤ 80 −100 mm   | 4           | 3      |